

PTS1P-NMDM-1M-P

PTS1-50-P SureFlex® Jumper with interface types N Male and 7-16 DIN Male, 1M



Product Classification

Product Type	SureFlex® Premium, static PIM
Product Series	PTS1-50-P

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD Static	-110 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2200 MHz	1.152	23.02
2200–2700 MHz	1.152	23.02

Jumper Assembly Sample Label

PTS1P-NMDM-1M-P



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

