

# C600-NMNM-80

---

CNT-600 CNT® Jumper with interface types N Male and N Male, 24.38 m



**OBSOLETE**

## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-600

## General Specifications

<b>Attachment, Connector A</b>	Field attachment
<b>Attachment, Connector B</b>	Field attachment
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CNT-600
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	N Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	24.38 m   79.987 ft
<b>Nominal Size</b>	0.600 in

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

# C600-NMNM-80

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 600BPNM-C – Type N Male for CNT-600 braided cable
- CNT-600 – CNT-600, CNT@ 50 Ohm Braided Coaxial Cable, black PE jacket