

1-1711613-2



Copper Patch Cord, 2P AMP TWIST to RJ45, S/FTP, LZSH, stranded, white, 1.5 m

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface, Connector B	2P AMP-TWIST plug
Jacket Color	White
Pairs, quantity	2

Dimensions

Cord Length	1.5 m 4.921 ft
Compatible Conductor Gauge, stranded	26 AWG

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

