

1-1711613-5



Copper Patch Cord, 2P AMP-TWIST to RJ45, S/FTP, LZSH, stranded, white, 15 m

OBSOLETE

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Asia Australia/New Zealand EMEA |
| Portfolio | NETCONNECT® |
| Product Type | Twisted pair patch cord |

General Specifications

| | |
|-------------------------------|-------------------|
| ANSI/TIA Category | 6A |
| Cable Type | S/FTP (shielded) |
| Conductor Type | Stranded |
| Interface, Connector A | RJ45 plug |
| Interface, Connector B | 2P AMP-TWIST plug |
| Jacket Color | White |
| Pairs, quantity | 2 |

Dimensions

| | |
|---------------------------------------------|------------------|
| Cord Length | 15 m 49.213 ft |
| Compatible Conductor Gauge, stranded | 26 AWG |

Environmental Specifications

| | |
|----------------------------|-------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

