



Copper Pigtail, 4P AMP-TWIST to Stub, category 7A, S/FTP, LSZH, white, 10 m

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Series</b>	SL Series

## General Specifications

<b>ANSI/TIA Category</b>	7A
<b>Cable Type</b>	S/FTP (shielded)
<b>Interface, Connector A</b>	4P AMP-TWIST Plug
<b>Interface, Connector B</b>	Unterminated
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4

## Dimensions

<b>Cord Length</b>	10 m   32.808 ft
<b>Compatible Conductor Gauge, solid</b>	22 AWG   22 AWG

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## Packaging and Weights

# 1-1711787-0

---

**Packaging quantity**

1

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

