

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 4 fibers, LC/APC to SC/APC, yellow, 13 m

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution cable assembly
Product Series	FPM

General Specifications

Color, boot A	Green
Color, boot B	Green
Color, connector A	Green
Color, connector B	Green
Connector A, quantity	4
Connector B, quantity	4
Construction Type	Stranded
Interface, Connector A	LC/APC
Interface, Connector B	SC/APC
Jacket Color	Yellow
Total Fibers, quantity	4

Dimensions

Cord Length	13 m 42.651 ft
--------------------	------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum, connector A	0.35 dB
Insertion Loss, maximum, connector B	0.35 dB
Return Loss, minimum, connector A	65 dB
Return Loss, minimum, connector B	65 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

