

# C400-SMQM-35

---

CNT-400 CNT® Jumper with interface types SMA Male and QMA Male,  
10.67 m



## Product Classification

<b>Product Type</b>	Braided cable assembly
<b>Product Brand</b>	CNT®
<b>Product Series</b>	CNT-400

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Cable Family</b>	CNT-400
<b>Interface, Connector A</b>	SMA Male
<b>Interface, Connector B</b>	QMA Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	10.67 m   35.007 ft
<b>Nominal Size</b>	0.400 in

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>700–3000 MHz</b>	1.433	14.99

## Jumper Assembly Sample Label

# C400-SMQM-35



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

- |             |   |
|-------------|---|
| 400PSM-CR   | - SMA Male for CNT-400 braided cable  |
| CNT-400     | - CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket   |
| CNT-400-SFR | - CNT-400-SFR, C CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, B2ca S1a d0 a1 Compliant |
| CNT-400-W   | - CNT-400-W, CNT® 50 Ohm Braided Coaxial Cable, variable, white PE jacket   |