imVision® imPower™



OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Portfolio	SYSTIMAX®	
Product Type	Network controller accessory	
Product Brand	imPower™ imVision®	

General Specifications

COIOI

Black

Dimensions

Height	43.18 mm 1.7 in
Width	76.2 mm 3 in
Depth	127 mm 5 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene	(ABS)	Polycarbonate
---------------	---------------------------------	-------	---------------

Environmental Specifications

Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

Page 1 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 22, 2021



760219345 | imV-imP

Safety Standard

C-tick | CE | GOST | KC | cUL

Packaging and Weights

Packaging quantity

Weight, net

0.045 kg | 0.1 lb

Regulatory Compliance/Certifications

1

AgencyClassificationCHINA-ROHSAbove maximum concentration valueROHSCompliant/Exempted



Page 2 of 2

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 22, 2021

