

Fiber Optic Simplex Connector Kit, Singlemode, slate



OBSOLETE

This product was discontinued on: **October 10, 2019**

Replaced By:

760242152
SFC-LCR-KSL

TeraSPEED® Pre-Radiused Keyed LC Connector for 900um & 1.6 mm fiber, simplex Singlemode, Slate

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Fiber connector
Product Series	SECURE

General Specifications

Application	For use with jacketed fiber cable
Body Style	Simplex
Boot Style	Bend limiting
Color	Slate
Color, boot	Blue
Interface	LC/UPC

Dimensions

Compatible Cable Diameter, maximum	2 mm 0.079 in
Compatible Cable Diameter, minimum	1.6 mm 0.063 in

Optical Specifications

1-1828079-0

Fiber Mode	Singlemode
Fiber Type	OS2

Packaging and Weights

Packaging quantity	10
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

