

## LightCrimp Plus™ Fiber Optic Connector Kit,, Singlemode

### **OBSOLETE**

This product was discontinued on: **March 30, 2022**

### **Replaced By:**

1985960-1

Fiber Optic Kit, LC, secure, simplex, Multimode, XG, red

## Product Classification

|                              |                              |
|------------------------------|------------------------------|
| <b>Regional Availability</b> | Australia/New Zealand   EMEA |
| <b>Portfolio</b>             | NETCONNECT®                  |
| <b>Product Type</b>          | Fiber connector              |
| <b>Product Brand</b>         | LightCrimp Plus™             |
| <b>Product Series</b>        | SECURE                       |

## General Specifications

|                          |                             |
|--------------------------|-----------------------------|
| <b>Application</b>       | For use with buffered fiber |
| <b>Body Style</b>        | Simplex                     |
| <b>Boot Style</b>        | Short                       |
| <b>Color</b>             | Red                         |
| <b>Color, boot</b>       | Blue                        |
| <b>Ferrule Geometry</b>  | Factory polished            |
| <b>Interface</b>         | LC/UPC                      |
| <b>Interface Feature</b> | Epoxyless                   |

## Dimensions

|                                  |                   |
|----------------------------------|-------------------|
| <b>Compatible Cable Diameter</b> | 0.9 mm   0.035 in |
|----------------------------------|-------------------|

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

# 1828856-1

---

**Packaging Type**                      Bag

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

