N.A

	INC.	REVISIONS										
				Р	LTR		DESCRIPTION		DATE	DWN	APVD	
	BY COMMSCOPE				B REV;	40032676MC0;	UPDATE LOG	0	01AUG2016	GG	SI	
	RITING											
	IN WE											
	AUTHORIZED IN WRITING	1. DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. (Nonimal values), VIEWS for REF. ONLY.										
	SPECIFIC PURPOSE											
2014	THE SP	3. GENERAL SPEC.: ISO/IEC 11801 Ed. 2.2										
	ONLY FOR	> IDC Capability:  >> AW G 22-26 Solid  >> AW G 24 Stranded.										
ATION	> Cable Jacket: Max. Ø 9.0 mm.											
PUBLICATION	4. RECOMMENDED PANEL CUT-OUT:											
RELEASED FOR P	4. RECOMMENDED PANEL CUT-OUT:  (for single wall plate & back panel for double wall plate) > Height: 19.30 (Nominal.) > Width: 14.73 (Nominal)											
LEASE	OPE,	> Width: 14.73 (Nominal)										
WWO JO										$\neg$		
	2016 ( PERTY (					17.2		38.30	_			
	ely PROF			T		T0-1	7	2.00	_		<b>_</b>	
	© 2016 BPEJEFGBNNGGNBVIARE AMPE EBRODMIASARU PROPERTY			Đ)/		CAT6A						
	IPE ESRA						01.9.30		١			
	/ IARÆ A∲						<u> </u>					
	NAGGNE			<b>~</b>	·		-	7.90				
].	JEFF (B)											
LI SHEL	AND BPE											
HST 1804ND	DAQMINGS A											
1 1	E DAGAW					A Cat	6	eries RJ45 Jack	21	53354-	1	
DRAWING 18	: THESE		4			A Cal	UA SIILU L SE	אוופא אוויי אפרו	Ζ Ι	-46	- 1	
	NOTICE:			_		REV.	DESCRI	PTION	PAR	T NUMI	BER	
	<u>'</u>	DIMENSIONS:	DWN A.CARRERAS	03MAR2014 PFRAS		. MATERIAL		FINISH				
	T/	OLERANCES UNLESS	CHK 03MAR201 L.de DIOS APVD 23JUN201 J.SANABRA		03MAR2014							
	ОТН	ERWISE SPECIFIED:			COMMSCOPE,			I, IIV				
	PLC	±- ±-	PRODUCT SPEC	_		NAME Cat6A Shld E Series						
2 F 3 F 4 F		±-		TION SPEC		RJ45 Jack			Т	DECT:	TEO T:	
ANGLES ±- 4				11-93030		SIZE CAGE C	DDE DRAWING NO			RESTRIC	IFD [O	
1		<del></del>	WEIGHT		-		G-215	3354 ———————————————————————————————————				

CUSTOMER DRAWING