


REVISIONS					
P	LR	DESCRIPTION	DATE	DWN	APVD
M		REV: EC 0210-0840-94	3-2-95	LM	NJ
N		REV PER BNS_CD_BRAND	01-31-17	GG	DC

- ① DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- ② MATERIAL: POLYESTER FILM 0.025 [.010] THICK. 2 LAYERS EACH SIDE. COPPER WIRE- 0.23 [.009] THICK x 15.24 [.600] WIDE. SHIELD- PVC, 0.025 [.010] THICK.
- ③ CABLE MARKED WITH COMMSCOPE PN 553239 TYPE FCC UL CSA 12 AWG, CU 300V, 20 AMP 60°C IN COLOR SPECIFIED FOR CONTINUOUS LENGTH OF ROLL AS SHOWN.
- ④ CAUTION: THE UNDERCARPET CABLE MAY NOT BE USED OUTDOORS OR IN WET LOCATIONS; WHERE THE CABLE WOULD BE SUBJECT TO CORROSIVE LOCATION; OR IN RESIDENTIAL, SCHOOL, AND HOSPITAL BUILDINGS.



30.7	[101]	3-553239-4
15.5	[51]	3-553239-3
76.5	[251]	3-553239-1
LENGTH PER ROLL - M [FEET]		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. SIMPSON 2-18-94	COMMSCOPE, INC.	
DIMENSIONS: mm [INCHES]		CHK C. WHITE	NAME CABLE, FLAT, 5 CONDUCTOR, 12 AWG, POWER, UNDERCARPET	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. MCNEIL D. MARGO	PRODUCT SPEC 108-6038	
0 PLC ± - ①			APPLICATION SPEC 114-6008	
1 PLC ± -			SIZE A1	
2 PLC ± -			CAGE CODE -	
3 PLC ± -			DRAWING NO C=553239	
4 PLC ± -			RESTRICTED TO -	
ANGLES ± -			SCALE -	
FINISH -			SHEET 1 OF 1 REV N	
MATERIAL ②			CUSTOMER DRAWING	