

# 760248203 | FT 3MM PVC SP 1200X1700UM PVDF BK



Furcation Tubing for Optical Fiber, indoor, Plenum PVC jacket, PVDF tubing, 1.20/3.00 mm, with strength member, black

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Furcation tubing

## General Specifications

<b>Application</b>	For use with all fiber connector types   For use with singlemode and multimode optical fibers
<b>Color</b>	Black

## Dimensions

<b>Length</b>	1000 m   3,280.84 ft
<b>Inner Diameter, nominal</b>	1.2 mm   0.047 in
<b>Outer Diameter, nominal</b>	3 mm   0.118 in

## Material Specifications

<b>Material Type</b>	PVC   PVDF
----------------------	------------

## Mechanical Specifications

<b>Minimum Bend Radius, Installation</b>	3 mm   0.118 in
<b>Minimum Bend Radius, Long Term</b>	5 mm   0.197 in
<b>Shrinkage, maximum</b>	5 %

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +70 °C (-32 °F to +158 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Indoor

# 760248203 | FT 3MM PVC SP 1200X1700UM PVDF BK

---

## Packaging and Weights

<b>Included</b>	Aramid strength members
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Reel
<b>Weight, net</b>	7.9 kg/km   5.309 lb/kft

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable