

# 760248205 | FT 3MM PVC SP 1200X1700UM PVDF RS



Furcation Tubing for Optical Fiber, indoor, Plenum PVC jacket, PVDF tubing, 1.20/3.00 mm, with strength member, rose

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Furcation tubing

## General Specifications

**Application** For use with all fiber connector types | For use with singlemode and multimode optical fibers

**Color** Rose

## Dimensions

**Length** 1000 m | 3,280.84 ft

**Inner Diameter, nominal** 1.2 mm | 0.047 in

**Outer Diameter, nominal** 3 mm | 0.118 in

## Material Specifications

**Material Type** PVC | PVDF

## Mechanical Specifications

**Minimum Bend Radius, Installation** 3 mm | 0.118 in

**Minimum Bend Radius, Long Term** 5 mm | 0.197 in

**Shrinkage, maximum** 5 %

## Environmental Specifications

**Installation temperature** 0 °C to +70 °C (-32 °F to +158 °F)

**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Environmental Space** Indoor

# 760248205 | FT 3MM PVC SP 1200X1700UM PVDF RS

---

## Packaging and Weights

<b>Included</b>	Aramid strength members
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Reel
<b>Weight, net</b>	7.9 kg/km   5.309 lb/kft

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable