


FD21204-48SRC-350



HELIAX® Pendant HCS 2.0; 6 x 24 hybrid cable includes 12-4AWG conductors x 48-single mode fibers. Top breakout (Pendant); 12 HQLC connectors with fiber and power outputs. Bottom breakout (BBU); blunt cut conductors and DLC connectors, 350 ft

- Note: 4AWG DC conductors are utilized for cable lengths 250 to 450 feet. 6AWG DC conductors are utilized for cable lengths 25 to 225 feet in the FD21206-48SRC-x product family

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	FD2

General Specifications

Conductors, quantity	12
Construction Type	Direct breakout trunk
Interface, Connector A	HQ-LC
Interface Feature, connector A	Outdoor
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Total Fibers, quantity	48

Dimensions

Cord Length	106.68 m 350 ft
Diameter Over Jacket	44.7 mm 1.76 in
Center Conductor Gauge	4 AWG
Center Conductor Gauge Note	4 AWG DC conductors for cable lengths from 250 to 450 feet

Mechanical Specifications

FD21204-48SRC-350

Minimum Bend Radius 360.7 mm | 14.201 in

Optical Specifications

Fiber Type G.657.A2/B2

Assembly Insertion Loss, typical 0.75 dB

Assembly Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Packaging and Weights

Cable weight 3.57 kg/m | 2.399 lb/ft

* Footnotes

Assembly Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)