



HGS620 Icon Strip (Voice / Data / Blank), White (25 ea/pkg)

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Icon kit |
| Ordering Note | Minimum order quantity, 20 packs |

General Specifications

| | |
|--------------|-------|
| Color | White |
|--------------|-------|

Dimensions

| | |
|---------------|--------------------|
| Height | 13.97 mm 0.55 in |
| Width | 23.62 mm 0.93 in |
| Depth | 2.79 mm 0.11 in |

Material Specifications

| | |
|----------------------|---|
| Material Type | High-impact, flame retardant, thermoplastic |
|----------------------|---|

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | UL cUL |

Packaging and Weights

| | |
|---------------------------|----|
| Packaging quantity | 25 |
|---------------------------|----|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

