

HGS620 Icon Strip (Voice / Data / Blank), Blue (25 ea/pkg)



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Icon kit
<b>Ordering Note</b>	Minimum order quantity, 20 packs

## General Specifications

**Color** Blue

## Dimensions

<b>Height</b>	13.97 mm   0.55 in
<b>Width</b>	23.62 mm   0.93 in
<b>Depth</b>	2.79 mm   0.11 in

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

**Packaging quantity** 25

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

