760238510 | OCC1P-10800-NNNQNQA-CL



OCC1P Wideband Splitter, planar, singlemode, 1x8, symmetrical split ratio, 0,250 mm cable, light duty housing

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Splitter component

Product Series OCC1P

General Specifications

Device Type Component, rectangular

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use in FOSC closures

Circuits, quantity 1

Distribution Type 1 x 8 splitter

Interface, InputStub tailInterface, OutputStub tail

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

Pigtail Length, Input
2.5 m | 8.202 ft

Pigtail Length, Output
2.5 m | 8.202 ft

Pigtail Diameter, Input
0.25 mm | 0.01 in

Pigtail Diameter, Output
0.25 mm | 0.01 in

Environmental Specifications



760238510 | OCC1P-10800-NNNQNQA-CL

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

