

# AT-30-UW-N-MFI6



20 dB Low PIM Attenuator 555–6000 NM-NF

## OBSOLETE

This product was discontinued on: May 14, 2023

### Replaced By:

AT-30-UW-43-MFI6      30 dB Low PIM Attenuator 555–6000 4.3-10 M-F

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Attenuator

## General Specifications

<b>Device Type</b>	Attenuator
<b>Application</b>	Indoor/Outdoor
<b>Color</b>	Silver
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	N Male
<b>Interface 2</b>	N Female
<b>Outer Contact Plating</b>	Trimetal

## Dimensions

<b>Height</b>	89 mm   3.504 in
<b>Width</b>	130 mm   5.118 in
<b>Length</b>	247 mm   9.724 in

## Electrical Specifications

<b>3rd Order IMD</b>	-163 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers
<b>Attenuation</b>	30 dB

# AT-30-UW-N-MFI6

---

<b>Attenuation Tolerance</b>	±1.5 dB
<b>Average Power, maximum</b>	100 W
<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	555 – 6000 MHz
<b>VSWR at Frequency Band</b>	1.25 @ 555–2700 MHz   1.3:1 @ 2700–6000 MHz

## Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +50 °C (-13 °F to +122 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP65

## Packaging and Weights

<b>Height, packed</b>	150 mm   5.906 in
<b>Width, packed</b>	225 mm   8.858 in
<b>Length, packed</b>	370 mm   14.567 in
<b>Weight, gross</b>	3.5 kg   7.716 lb
<b>Weight, net</b>	2.9 kg   6.393 lb