

# E33984-000 | OCC1D-X-530-NNNQF

---



OCC1D DWDM, 1 channel, double demux, 1535.04 nm starting wavelength, 0.250 mm cable, light duty housing, field installable

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	DWDM component
<b>Product Series</b>	OCC1D

## General Specifications

<b>Device Type</b>	Component, rectangular
<b>Functionality</b>	Demultiplexing
<b>Technology Type</b>	Thin film filter (TFF)
<b>Application</b>	For use in FOOSC closures
<b>Circuits, quantity</b>	2
<b>Distribution Type</b>	1-channel DWDM
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail
<b>Multiplexers, quantity</b>	2

## Dimensions

<b>Pigtail Length, Input</b>	2.5 m   8.202 ft
<b>Pigtail Length, Output</b>	2.5 m   8.202 ft
<b>Pigtail Diameter</b>	0.25 mm   0.01 in

## Optical Specifications

<b>Starting Wavelength</b>	1,535.04 nm
----------------------------	-------------

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

