

# 19256B-D

---

## Lace-up Hoisting Grip with Security Clamp for HELIAX® Cables



**OBSOLETE**

### Product Classification

<b>Product Type</b>	Hoisting grip
<b>Ordering Note</b>	CommScope® Standard Product in Europe

### General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Lace-up hoisting grip
<b>Support Clamp</b>	Included
<b>Tool Type</b>	Hoisting grip

### Dimensions

<b>Grip Length, minimum</b>	431.8 mm   17 in
<b>Leader Length, minimum</b>	330.2 mm   13 in
<b>Nominal Size</b>	7/8 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Mechanical Specifications

<b>Pull Load Capacity</b>	226.796 kg   500 lb
---------------------------	---------------------

# 19256B-D

---

## Packaging and Weights

<b>Height, packed</b>	38.1 mm   1.5 in
<b>Width, packed</b>	218.44 mm   8.6 in
<b>Length, packed</b>	220.98 mm   8.7 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.22 kg   0.485 lb