2105082



Fiber Optic Patch Cord, Simplex, 0.9mm, Singlemode, SC/UPC to SC/UPC, Yellow

Fiber Optic Patch Cord, Simplex, 0.9mm,SM, SC/UPC to SC/UPC, LSZH,Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand China India	
Portfolio	CommScope®	
Product Type	Fiber patch cord, simplex	
General Specifications		
Connector A, quantity	1	
Color, boot A	Blue	
Color, connector A	Blue	
Connector B, quantity	1	
Color, boot B	Blue	
Color, connector B	Blue	
Interface, Connector A	SC/UPC	
Interface, Connector B	SC/UPC	
Jacket Color	Yellow	
Total Fibers, quantity	1	
Dimensions		
Cable Assembly Length Range (m)	1 – 999	
Cable Assembly Length Range (ft)	1 – 999	
Diameter Over Jacket	0.9 mm 0.035 in	
Mechanical Specifications		
Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °	
Optical Specifications		
Fiber Mode	Singlemode	
Fiber Type	G.657.A1, TeraSPEED®	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2023



2105082

Insertion Loss, maximum	0.25 dB
Return Loss, minimum	50 dB

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 1

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2023

