FGS-HTHR-16MM-30CM



FiberGuide® Threaded Rod, 16mm Diameter, 30cm Length

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Threaded rod
Product Brand FiberGuide®

Product Series FGS

General Specifications

Color Silver

Orientation Horizontal
Section Type Mounting

Dimensions

Length mm | 11.811 in

Rod Length 300 mm | 11.811 in


Thread Size 16 mm

System Dimensions 102 mm x 102 mm (4 in x 4 in) | 102 mm x 152 mm (4 in x 6 in) | 51 mm x 152 mm (2 in x 6 in)

Ordering Tree



FGS-HTHR-16MM-30CM



Rod Diameter

9	1/2	1/2 in	
	5/8	5/8 in	
	12 MM	12 mm	
	14 MM	14 mm	
	16 MM	16 mm	

^{*} Rod diameter and length needs to be both metric or imperial sized

Rod Length

10	12	12 in
10	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

Packaging and Weights

Weight, net 0.37 kg | 0.816 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

