## FGSB-MVAR-B



#### FiberGuide® Expandable Straight Section, 4x6in, Black

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Expandable straight

Product Brand FiberGuide®

Product Series FGS

## General Specifications

**Color** Black

**Orientation** Horizontal

Section Type Straight section

#### **Dimensions**

 Height
 101.6 mm | 4 in

 Width
 152.4 mm | 6 in

 Length
 356 mm | 14.016 in

**System Dimensions** 102 mm x 152 mm (4 in x 6 in)

#### Material Specifications

Material Type Engineering Thermoplastic

## **Environmental Specifications**

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

## Packaging and Weights

**Weight, net** 0.985 kg | 2.172 lb

COMMSC PE°

# FGSB-MVAR-B

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

