

SVWPWF81GA



HomeConnect® Wall Plate, white, with F81 barrel splice

OBSOLETE

Product Classification

Product Type	Wall plate
Product Brand	HomeConnect®

General Specifications

Color	White
Mounting	Flush

Dimensions

Length	28.194 mm 1.11 in
---------------	---------------------

Electrical Specifications

Insertion Loss at Frequency Band, maximum	0.2 dB @ 0–1002 MHz 0.3 dB @ 1002–3000 MHz
Return Loss at Frequency Band, minimum	20 dB @ 2000–3000 MHz 25 dB @ 1002–2000 MHz 35 dB @ 0–1002 MHz
Impedance	75 ohm
Operating Frequency Band	0 – 3000 MHz
Shielding Effectiveness, minimum	120 dB

Material Specifications

Material Type	Brass Plastic
Plating	Nickel

SVWPWF81GA

Environmental Specifications

Safety Standard CE | EN 60728-4 | SCTE

Packaging and Weights

Height, packed 292.1 mm | 11.5 in

Width, packed 254 mm | 10 in

Length, packed 647.7 mm | 25.5 in

Packaging quantity 250

Weight, gross 9.072 kg | 20 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

SVF81GA – HomeConnect® F81 Barrel Splice, sealing surface