



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 10 mm/3 mm Shrink ratio, 1500 mm long, hotmelt adhesive, 15 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

## Product Classification

|                              |                                 |
|------------------------------|---------------------------------|
| <b>Regional Availability</b> | EMEA                            |
| <b>Product Type</b>          | Heat shrink tubing, medium wall |
| <b>Product Series</b>        | MWTM                            |

## General Specifications

|                     |                  |
|---------------------|------------------|
| <b>Color</b>        | Black            |
| <b>Sealant Type</b> | Hotmelt adhesive |

## Dimensions

|   |                     |
|---|---------------------|
| <b>Length</b>                             | 1500 mm   59.055 in |
| <b>Expanded Inside Diameter, minimum</b>  | 10 mm   0.394 in    |
| <b>Recovered Inside Diameter, maximum</b> | 3 mm   0.118 in     |
| <b>Recovered Wall Thickness, minimum</b>  | 1 mm   0.039 in     |

## Material Specifications

|                      |            |
|----------------------|------------|
| <b>Material Type</b> | Polyolefin |
|----------------------|------------|

## Environmental Specifications

|                            |                 |
|----------------------------|-----------------|
| <b>Environmental Space</b> | Aerial   Ducted |
|----------------------------|-----------------|

## Packaging and Weights

|                           |              |
|---------------------------|--------------|
| <b>Packaging quantity</b> | 15           |
| <b>Packaging Type</b>     | Bag   Carton |

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS

ROHS



**Classification**

Below maximum concentration value

Compliant