



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 25 mm/8 mm Shrink ratio, 1000 mm long, hotmelt adhesive, 10 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Heat shrink tubing, medium wall
<b>Product Series</b>	MWTM

## General Specifications

<b>Color</b>	Black
<b>Sealant Type</b>	Hotmelt adhesive

## Dimensions

<b>Length</b>	1000 mm   39.37 in
<b>Expanded Inside Diameter, minimum</b>	25 mm   0.984 in
<b>Recovered Inside Diameter, maximum</b>	8 mm   0.315 in
<b>Recovered Wall Thickness, minimum</b>	2 mm   0.079 in

## Material Specifications

<b>Material Type</b>	Polyolefin
----------------------	------------

## Environmental Specifications

<b>Environmental Space</b>	Aerial   Ducted
----------------------------	-----------------

## Packaging and Weights

<b>Packaging quantity</b>	10
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

