


760236259 | FOSC-OC-3DSD1254NN2T-U23

FOSC® D-TRAY-72 type, DWDM, 16 channels, demux, 1557.36 nm starting wavelength, 100 GHz channel spacing + upgrade



Product Classification

Regional Availability	North America
Product Type	DWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Dimensions

Height	375.92 mm 14.8 in
Width	152.4 mm 6 in
Depth	10.67 mm 0.42 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

