

876696-000 | FOSC-OC-6DAX1324NN2T-U23



FOSC® A-TRAY-24 type, DWDM, 4 channels + upgrade port, double demux, 1551.72 nm starting wavelength, 100 GHz channel spacing + upgrade

Product Classification

Regional Availability	North America
Product Type	DWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Dimensions

Height	233.68 mm 9.2 in
Depth	10.67 mm 0.42 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

