

209800-15B



Self-locking Hanger for 1/2 in RCT4 RADIAX® Radiating cable

OBSOLETE

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1
Color Black
Hanger Type Self locking hanger

Dimensions

Maximum Stack Height 2
Height 32 mm | 1.26 in
Width 17 mm | 0.669 in
Length 20.6 mm | 0.811 in
Compatible Diameter, maximum 16.8 mm | 0.661 in
Compatible Diameter, minimum 14.3 mm | 0.563 in
Nominal Size 1/2 in

Material Specifications

Material Type Polyamide PA12

Mechanical Specifications

Maximum Load 650 N | 146.126 lbf

209800-15B

Environmental Specifications

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Flammability Test Method	UL 94-HB
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	≥500 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	10 cm 3.937 in
Width, packed	11.5 cm 4.528 in
Length, packed	18 cm 7.087 in
Packaging quantity	100
Weight, gross	0.5 kg 1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power