

# 35849A-17



Single Entrance Panel for elliptical waveguide 34

**OBSOLETE**

## Product Classification

**Product Type** Entrance panel

## General Specifications

**Color** Gray  
**Entry Panel Port Size** 127 mm | 5 in  
**Number of Ports** 1  
**Panel Type** Single

## Dimensions

**Height** 50.8 mm | 2 in  
**Width** 215.9 mm | 8.5 in  
**Waveguide Size** WR229 | WG11 | R40

## Material Specifications

**Material Type** Galvanized steel

## Environmental Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

## Packaging and Weights

**Height, packed** 609.6 mm | 24 in  
**Width, packed** 279.4 mm | 11 in

# 35849A-17

---

<b>Length, packed</b>	279.4 mm   11 in
<b>Included</b>	Boot   Clamp   Plate
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	4.37 kg   9.634 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

