

BHD-114



Double Block Hanger for 1-1/4 in coaxial cable

Product Classification

Product Type	Hanger kit
Ordering Note	CommScope® standard product (Global)

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Double block hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	3
Height	49 mm 1.929 in
Width	56.1 mm 2.209 in
Length	110 mm 4.331 in
Compatible Cable Diameter Range	39.6–40.6 mm
Compatible Diameter, maximum	40.6 mm 1.598 in
Compatible Diameter, minimum	39.6 mm 1.559 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Environmental Specifications

BHD-114

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	5.1 cm 2.008 in
Width, packed	20.3 cm 7.992 in
Length, packed	30.5 cm 12.008 in
Packaging quantity	10
Weight, gross	0.99 kg 2.183 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power