


# CK6003-000 | FOSC-OC-3D8M1212NN

FOSC® D-TRAY-72 type, DWDM, 8 channels, mux, 1560.61 nm starting wavelength, 200 GHz channel spacing



## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	DWDM splice tray
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC-OC

## General Specifications

<b>Application</b>	For use in FOSC closures
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail

## Dimensions

<b>Height</b>	375.92 mm   14.8 in
<b>Width</b>	152.4 mm   6 in
<b>Depth</b>	10.67 mm   0.42 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

