

FA-3540-STH



Standard Butterfly Hanger and Grommet kit for HELIAX® Cables, 35-40mm

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1
Color Black | Silver
Hanger Type Hanger kits
Mounting 3/8 in (M10) drilled cable ladder

Dimensions

Height 51.1 mm | 2.012 in
Compatible Diameter, maximum 40 mm | 1.575 in
Compatible Diameter, minimum 35 mm | 1.378 in
Nominal Size 1-5/8 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB
DTF Effect, maximum 0.1 dB

Material Specifications

Material Type EPDM rubber | Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

FA-3540-STH

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight

Packaging and Weights

Height, packed	26 cm 10.236 in
Width, packed	9 cm 3.543 in
Length, packed	9 cm 3.543 in
Packaging quantity	10
Weight, gross	0.53 kg 1.168 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

