

L45SGRIP



Support Hoisting Grip for 5/8 in coaxial cable

OBSOLETE

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	254 mm 10 in
Leader Length, minimum	304.8 mm 12 in
Nominal Size	5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

L45SGRIP

Pull Load Capacity 226.796 kg | 500 lb

Packaging and Weights

Packaging quantity 1

Weight, gross 0.3 kg | 0.661 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system