FD4S-A072J00GAB1



FDH 4000, 72 distribution fibers, no splitters loaded, SC/APC, single armor, loose tube, 100 ft stub

- Thermoplastic construction provides UV stabilization, flame retardancy, and chemical & impact resistance
- ٠ Provides air/water tight seal ensuring protection from flooding and fungus
- ٠ Unsurpassed reliability makes it ideal for aerial and below grade applications
- Supports diverse Plug-and-Play splitter and xWDM module Configurations ٠

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber distribution closure
Product Series	FDH 4000

General Specifications

Access	Front
Cable Type	Armored - Single Loose Tube
Color	Black
Distribution Cables, quantity	1
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Handhole Pole Wall
Splitter Slots, quantity	11
Dimensions	
Height	685.8 mm 27 in
Width	241.3 mm 9.5 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small


Dimension Drawing


Page 1 of 3


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 29, 2024



FD4S-A072J00GAB1








Ordering Tree

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 29, 2024

COMMSCOPE°

FD4S-A072J00GAB1



Environmental Specifications

Environmental Space	Above ground Aerial Below ground
Qualification Standards	IEC 60529, IP68 Telcordia GR-3121-CORE Telcordia GR-3125-CORE
Packaging and Weights	
Packaging quantity	1
Packaging Type	Pallet
Weight, net	15.876 kg 35 lb

Regulatory Compliance/Certifications

CHINA-ROHS Above maximum concentration value ROHS Compliant/Exempted	Agency	Classification
ROHS Compliant/Exempted	CHINA-ROHS	Above maximum concentration value
	ROHS	Compliant/Exempted
UK-ROHS Compliant/Exempted	UK-ROHS	Compliant/Exempted



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 29, 2024

