LS2-HMHM-1M-W1-D



LSF2 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing on one end only, $1\,\mathrm{m}$

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series LSF2-50

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector A4.3-10 MaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 1 m | 3.281 ft

Nominal Size 3/8 in

Electrical Specifications


3rd Order IMD -119 dBm

3rd Order IMD Test Method Two +43 dBm carriers

Logo Image



LS2-HMHM-1M-W1-D



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-970 MHz	1.065	30
1700-2200 MHz	1.065	30
2200-2700 MHz	1.083	28
3400-3800 MHz	1.222	20
4000-6000 MHz	1.222	20

Jumper Assembly Sample Label

LS2-HMHM-1M-W1-D



Environmental Specifications

Immersion Test MethodMeets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX® SureGuard weatherproofing boot

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

LSF2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket

(Not for Individual Sale - Jumpers only)

P4HM-S2 - 4.3-10 Male for 3/8 in LSF2-50 cable, factory attached

