

SHK-30-1-P-10



Hanger Kit for single stack of RFF cable; includes ten sets of hardware, angle adapters and rubber grommets

OBSOLETE

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	1
Height	55.1 mm 2.169 in
Width	59.9 mm 2.358 in
Length	171 mm 6.732 in
Compatible Diameter, maximum	26.4 mm 1.039 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Engineered plastic Stainless steel
----------------------	--

SHK-30-1-P-10

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 0 cm | 0 in

Width, packed 0 cm | 0 in

Length, packed 0 cm | 0 in

Included Angle adapter | Hardware | Rubber grommet

Packaging quantity 10

Weight, gross 2.8 kg | 6.173 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power