MHBD-FOC1A



Hardened Multifiber Optical Connector (HMFOC) cable assembly, HMFOC plug to 12 SC/UPC, 12-fiber

Product Classification

Product Type Fiber drop cable assembly

Product Series MHBD

Ordering Note For custom cable assembly lengths, please contact your local CommScope

representative

General Specifications

Cable TypeDielectric - Flat

Connector A, quantity

Color, boot ABlackColor, connector ABlackConnector B, quantity12

Color, boot B Blue
Color, connector B Blue

Interface, Connector A Hardened multi-fiber (HMFOC) plug

 Interface Feature, connector A
 Female

 Interface, Connector B
 SC/UPC

 Jacket Color
 Black

 Total Fibers, quantity
 12

Dimensions

Breakout Length, connector B 711.2 mm | 28 in

Cable Assembly Length Range (m) 1 - 900


Cable Assembly Length Range (ft) 10 - 1000

Cable Outer Diameter 4.5 x 8.0 mm (0.18 x 0.31 in)


Ordering Tree



MHBD-FOC1A



Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded88.9 mm3.5 inMinimum Bend Radius, unloaded63.5 mm2.5 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Page 2 of 3

MHBD-FOC1A

Insertion Loss, maximum, connector A0.45 dBInsertion Loss, maximum, connector B0.4 dBReturn Loss, minimum, connector A65 dBReturn Loss, minimum, connector B55 dB

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-22 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Storage Temperature $-40 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F})$

Environmental Space Outdoor, buried

Jacket UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1