760244300 | FD-N012A-0300F



Product Classification

Fiber Optic Cable Assembly, 12 SC/UPC to Stub, 12-fiber, 300 Feet

| Regional Availability | Australia/New Zealand EMEA Latin America North America | |
|--------------------------------|--|--|
| Product Type | Fiber drop cable assembly | |
| Product Series | FD | |
| General Specifications | | |
| Cable Type | Dielectric - Flat | |
| Connector A, quantity | 12 | |
| Color, boot A | Blue | |
| Color, connector A | Blue | |
| Construction Type | Breakout, armored | |
| Interface, Connector A | SC/UPC | |
| Interface Feature, connector A | Male | |
| Interface, Connector B | Unterminated | |
| Jacket Color | Black | |
| Total Fibers, quantity | 12 | |
| Dimensions | | |
| Cable Assembly Length | 91.44 m 300 ft | |
| Cable Outer Diameter | 4.3 x 8.0 mm (0.17 x 0.31 in) | |


Representative Image

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024



760244300 | FD-N012A-0300F



Mechanical Specifications

| 86 mm 3.386 in |
|----------------------|
| 81 mm 3.189 in |
| |
| Singlemode |
| G.657.A2, TeraSPEED® |
| 0.4 dB |
| 65 dB |
| |

Environmental Specifications

| Installation temperature | -30 °C to +70 °C (-22 °F to +158 °F) |
|--------------------------|---|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +75 °C (-40 °F to +167 °F) |
| Environmental Space | Outdoor, buried |
| Jacket UV Resistance | UV stabilized |
| Qualification Standards | IEC 60529:2001, IP68 Telcordia GR-326 |

Packaging and Weights

Packaging quantity

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

1

COMMSCOPE°

760244300 | FD-N012A-0300F

Regulatory Compliance/Certifications

Agency

ROHS **UK-ROHS**

Classification

CHINA-ROHS ISO 9001:2015

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted



Compliant/Exempted

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

