XA-2030



Crossover Angle, 2.38 in to 2.88 in OD

Product Classification

Product Type Mounting kit

General Specifications

Tower Taper Non-tapered

Dimensions

 Height
 152.4 mm | 6 in

 Width
 152.4 mm | 6 in

 Length
 152.4 mm | 6 in

 Mounting Diameter, maximum
 73.66 mm | 2.9 in

 Mounting Diameter, minimum
 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Angle | U-bolts

Packaging quantity 2

Weight, net 1.8 kg | 3.968 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



XA-2030





