

VIP7100 UHD IP Streamer

IP, HEVC, Ultra-HD Streamer with pre-certified Android TV[™] and Netflix[®]



FEATURES

- Android TV 10 certified
- Netflix certified
- Voice-enabled remote
- Interactive IP set-top supports standard Android TV applications as well as Google casting from phone to Set-top
- Industry-standard DRM support including pre-integration with Microsoft® PlayReady®, Widevine®.
- Ultra-HD with a HDR10 and HLG.
- Wi-Fi[®] 5 (802.11ac)
- HDMI[™] 2.1 and HDCP 2.2
- Secure Bootloader
- Low-power, compliant with EU power consumption regulations

PRODUCT OVERVIEW

A stylish, high-quality UHD (4K) streamer/IP set-top in a compact form factor, certified with Android TV, which uses the latest technologies to reduce power consumption and increase processing capabilities.

High Quality Video Experience - Ultra-HD, 10-bit colour and High Dynamic Range deliver four times the resolution of full HD, improved colour reproduction and a wider luminance range for an image that's even closer to reality, all at frame rates that allow fast-moving action with reduced blurring.

High Efficiency Video Coding (HEVC/H.265) offers up to 50% bandwidth saving compared to the H.264 standard. HEVC can be used by operators to deliver a superior quality-of experience within the same bandwidth or to increase their existing capacity by re-encoding existing assets.

Enables a wide choice of User Experiences – a high-performance processor, 3D OpenGL and fast memory gives the platform the power to support a wide range of applications to deliver a modern user experience.

Connectivity – 100 Mb/s Ethernet and Wi-Fi 5. One USB 3.0 and one USB 2.0 allows the connection of additional storage devices for functions such as offline storage. The Bluetooth Low Energy remote control option supports voice search and allows for hidden installation.

© 2021 CommScope, Inc. All rights reserved.

Ultra High Definition

HEVC H.265

HDMI[™] 2.1



GENERAL SPECIFICATIONS

Core Processor		
Processing	Quad-core, 16500 DMIPS	
Graphics		
Technology	3D OpenGL ES3.0	
Memory		
RAM	2 GB DDR3	
Application Flash	8 GB eMMC	
Network		
Ethernet	10/100 Full duplex	
Wi-Fi	802.11 a/b/g/n/ac	
Video Decode / Encode		
Decoders/Resolutions	Single up to 4Kp60 10bit	
HDR formats supported	HDR10, HLG	
Encoders	None	
Profiles	HEVC H.265 up to Main10@L5.1; AVC H.264 up to MP@L4.2; MPEG-2 up to MP@HL VP9 Profile 0 and 2	
Audio Decode		
Sample Rate	32-192 kHz	
MPEG Audio	MPEG-1 Layers 1, 2, and 3 (MP3)	
MPEG-4 Audio	HE AAC v2 profile	
Dolby	Dolby Digital™, Dolby Digital Plus™, and Dolby ATMOS™ (pass through)	
Power		
EU Code-of-Conduct compliant		
Compliant to Energy Using Products Legislation EC No 1275/2008 and amendment EU 801/2013		

GENERAL SPECIFICATIONS - CONTINUED		
Front Panel		
Remote Control	Bluetooth, IR	
Indicators	LED, Blue/Red	
Right side panel		
USB	USB 3.0 & USB 2.0 Type A 500 mA	
Reset button	Pinhole	
Rear Panel		
Digital AV	HDMI™ 2.1	
Analogue AV	3.5mm jack	
Digital Audio	Toslink	
USB	USB 3.0 & USB 2.0 Type A 500 mA	
Ethernet	RJ-45 Fast Ethernet	
Power	DC input	
CAS and Security		
Secure Processor	Yes	
HDCP	HDCP 2.2	
DRM Support	Microsoft PlayReady® Widevine®	

Physical	
Dimensions	105mm (W) x 105mm (D) x 20.5mm (H)
Weight	165g
Units per master carton	10
Master carton per pallet	40
Minimum order quantity	400



DOLBY AUDIO

CUSTOMER CARE

External PSU, localised according to region

Contact Customer Care for product information and sales:

United States: 866-36-ARRIS

• International: +1-678-473-5656



Toolkit. (http://www.OpenSSL.org/)



VIP7100 – UHD IP Set-Top

Note: Specifications are subject to change without notice. Copyright Statement: © 2021 CommScope, Inc. All rights reserved. ARRIS and the ARRIS logo are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc. and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

(x1 06-2021)