

# RA-38C



PIM-free, stand off adapter that can be strapped to round or angle member towers to attach a 3/8" threaded rod or snap-in hangers

- Adapts 3/8 inch threaded rods to round members and tower angles up to 1/4 inch
- Adapts snap-in hangers to round members and tower angles up to 1/4 inch
- Optimized to reduce PIM while maximizing structural integrity

## Product Classification

Product Type	Adapter
Product Brand	PIM-guard
Ordering Note	CommScope® standard product (Global)

## General Specifications

Adapter Type	Stand-off adapter
Color	Black
Mounting	3/4 in through hole   3/8 in through hole

## Dimensions

Height	40.894 mm   1.61 in
Outside Width	35.052 mm   1.38 in
Outside Length	50.038 mm   1.97 in

## Material Specifications

Material Type	Engineered plastic
---------------	--------------------

## Mechanical Specifications

Maximum Loading	Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411, SSH-1117   Triple stack, 1/2 in cable
Vibration Survival	≥4 hours at resonant frequency

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours

# RA-38C

---

## Packaging and Weights

Height, packed	17 cm   6.693 in
Width, packed	13 cm   5.118 in
Length, packed	10 cm   3.937 in
Packaging quantity	10
Weight, gross	0.27 kg   0.595 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

