

FPX EMPTY PANELS



The FPX series panels can be purchased empty. In this form, the end-user can mix and match any combination of modular FPX adapter packs or modules or simply utilize a “grow as you go” approach to their network.

CommScope’s FPX series provides industry-leading fiber cable protection and management in a modular footprint. With a depth of 12.0” and with front only as well as front and rear access, the FPX panel is suitable for a wide range of applications including central offices, data centers, indoor and outdoor cabinets, huts, CEV’s and more.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FPX

General Specifications

Growth Configuration	Unloaded
Rack Type	EIA 19 in EIA 23 in
Shelf Movement	Sliding

Dimensions

Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)