

FPX PRE TERMINATED PANELS



To accommodate varying network requirements and fast installation, the FPX series fiber panels are available preterminated with either intrafacility cable (IFC) or outside plant (OSP) cables

CommScope's FPX series provides industry-leading fiber cable protection and management in a modular footprint. With a depth of 12.0" and with front only as well as front and rear access, the FPX panel is suitable for a wide range of applications including central offices, data centers, indoor and outdoor cabinets, huts, CEV's and more.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Series	FPX

General Specifications

Growth Configuration	Fully loaded
Rack Type	EIA 19 in EIA 23 in
Shelf Movement	Sliding

Dimensions

Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)