UBWLCUC11



TeraSPEED® LC/UPC to Unconnectorized, Fiber Pigtail, 0.9 mm SBJ

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber pigtail, unjacketed

Product Brand SYSTIMAX InstaPATCH® 360

Ordering Note Minimum length may vary based on cable configuration


General Specifications

Color, boot A Blue
Color, connector A Blue
Interface, Connector A LC/UPC
Jacket Color Yellow
Total Fibers, quantity 1

Dimensions

Cable Assembly Length Range (m) 1 - 20
Cable Assembly Length Range (ft) 1 - 66

Ordering Tree



COMMSCOPE®

UBWLCUC11

Mechanical Specifications

Cable Retention Strength, maximum 2.00 lb @ 90° | 5.00 lb @ 0°

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 2

Included Products

Fiber Indoor Cable, TeraSPEED® 0.9 mm Low Smoke Zero Halogen Reinforced Buffered, 1 760004564 N-001-RF-8W-F09YL

fiber, Singlemode G.652.D and G.657.A1, Gel-free, Feet jacket marking, Yellow jacket color

LC/UPC Connector, Singlemode, Blue 860657286