

SSC-760241465N4U | 12 in Pole Top with ant concealment for Nokia



Washington DC Approved Top of Pole 12in Dia Concealment Enclosure for up to two Airscale Micro radios and/or LAA/CBRS radios or one Samsung LAA or CBRS

- Enclosure for holding 2 Nokia Airscale Micro LAA/CBRS radios
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment with a shroud that is 12" in diameter and 62" tall that can accommodate CommScope as well as most antenna manufacturers antennas that are less than 12" in diameter. Please reach out to your CommScope Representative for exact model number.

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

See compatibility matrix for compatible antennas

-Supports (1) "RT4401-48A" or (1) "RT2201-46A" Samsung radio with included adapter bracket. Power Supply to be located in mid pole enclosure.

-Supports AWHQN with separately available kit "860664329-AMK-001"

-Supports DK antenna with separately ordered "MTM106001" bracket.

Product Classification

Portfolio	CommScope®
Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	GALTRONICS GAMMA NU ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Black (RAL 9005)
Cooling	Passive Cooling
Mounting Options	Concrete poles Metal poles Non-tapered poles Tapered poles Wood

SSC-760241465N4U | 12 in Pole Top with ant concealment for Nokia

poles

Radio Compatibility, Nokia

(2) Airscale micro radios (Including LAA & CBRS models) | AHIA | AHIB | AZRB

Radio Compatibility Samsung

RT2201-46A | RT4401-48A

Radios Included

None

Dimensions

Height

1,574.8 mm | 62 in

Width

304.8 mm | 12 in

Depth

304.8 mm | 12 in

Mounting Bolt Circle Diameter

142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum

Chromate

Finish Concealment Covers

Powder coated

Material Type

Aluminum | Steel

Environmental Specifications

Thermal Compliance

GR-487

Packaging and Weights

Volume

0.056 m³ | 1.97 ft³

Weight (unloaded)

18.144 kg | 40 lb

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines