

# CLT4HM-CO

---



MQ Multiport cluster 4 ports cable assembly with interface type MQ female to 4.3-10 male, size 1/4"

## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	MQ
<b>Warranty</b>	Two years

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Interface, Connector A</b>	MQ Female
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Nominal Size</b>	1/4 in
---------------------	--------

## Port Configuration

Pin Assignment	Label
1	MQ4-1 (R-)
2	MQ4-2 (CR-)
3	MQ4-3 (CL-)
4	MQ4-4 (L-)

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	25.4 mm   1 in
<b>Minimum Bend Radius, single Bend</b>	25.4 mm   1 in

# CLT4HM-CO

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Immersion Test Method</b>	IEC 60529, IP67

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--