

VSRC-TL-B



Interlocking Channel V-Stabilizer™ for Tower Legs 8-16in OD- Adjustable from 34.5" to 57.5" Plus Vertical & Horizontal Adjustments

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 406.4 mm (16 in) | Angle 90°, 304.8 mm (12 in)

Pipe, quantity 0

Sectors, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Length 1,460.5 mm | 57.5 in

Mounting Diameter, maximum 406.4 mm | 16 in

Mounting Diameter, minimum 203.2 mm | 8 in

Stand-off Distance, adjustable 34.5–57.5 in | 87.6–146 cm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity 1

Weight, net 61.326 kg | 135.2 lb