U3VQPQXTK

Base Product



Ultra Low Loss (ULL) OM5 MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 72-Fiber, LZSH B2ca

Product Classification

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity 9

Color, boot A Gray

Color, connector A Lime green

Connector B, quantity 9

Color, boot B Gray

Color, connector BLime greenConstruction TypeStrandedFurcation ColorLime green

Interface, Connector A MPO-08/UPC Female

Interface, Connector B MPO-08/UPC Male

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 72

Dimensions

Breakout Length 22 in


Cable Assembly Length Range (m)

3 - 305

Cable Assembly Length Range (ft)

10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

-10 °C to +60 °C (+14 °F to +140 °F) **Operating Temperature**

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Classification **Agency ANATEL** Compliant ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





U3VQPQXTK

Included Products

760253112 N-072-MP-5G-F08LM/20T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 72 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM5, Meters jacket marking, Lime green jacket color, B2ca flame rating

860659020 – MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm 860659026 – MPO-08, ULTRA LOW LOSS, FEMALE, OM5, LIME-GREEN, 2mm



760253112 | N-072-MP-5G-F08LM/20T/B2



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 72 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM5, Meters jacket marking, Lime green jacket color, B2ca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 8

Fibers per Subunit, quantity 8

Total Fiber Count 72

Dimensions


Buffer Tube/Subunit Diameter 2 mm | 0.079 in

Diameter Over Jacket 10.7 mm | 0.421 in

Representative Image



760253112 | N-072-MP-5G-F08LM/20T/B2



Mechanical Specifications

Minimum Bend Radius, loaded 161 mm | 6.339 in

Minimum Bend Radius, unloaded 107 mm | 4.213 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 187 m | 613.517 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $0 \, ^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Page 5 of 10



760253112 | N-072-MP-5G-F08LM/20T/B2

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

1666 | UL 1685

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

 Low High Bend
 0 °C to +60 °C (+32 °F to +140 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

Temperature Cycle $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 118 kg/km | 79.292 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 8

Dimensions

Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance ROHS Compliant Compliant



UK-ROHS



MPO-08, ULTRA LOW LOSS, FEMALE, OM5, LIME-GREEN, 2mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandLazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Female

Interface Feature Unpinned

Total Fiber Count 8

Dimensions

Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

